



SWISS QUALITY.
SINCE 1938.



CARBOFIL™


Depth filter media with immobilized carbon

DEPTH FILTRATION FOR VALUABLE LIQUIDS. SINCE 1938.

Introduction


Powdered activated carbons (PAC) play a critical role in a vast and diverse range of applications. Decolorization, deodorization or the removal of other trace impurities are amongst the most common applications where PAC are widely used in the pharmaceutical as well as in the food & beverage industries. Due to their unique adsorption characteristics, PAC are also used in biotechnological processing and the production of fine chemicals. In order to meet these various demands, there are a large number of activated car-

bons available, offering different levels of activation, molecular structure and purity levels. Using activated carbon in an immobilized form (e.g. in a depth filter sheet or lenticular module) offers significant benefits in handling, cleaning and time (cost savings), compared to using PAC. FILTROX CARBOFIL™ products bring out all the benefits of immobilized activated carbon versus PAC. Furthermore, the adsorption efficiency of immobilized activated carbon is higher than with an equivalent amount of bulk PAC.



Pore size distribution


Activated carbon is a highly porous adsorptive material. Organic contaminants get trapped within the pores. Pore sizes vary between micropores, mesopores and macropores with various pore size distribution patterns amongst different activated carbons, depending on the activation method and the material source involved.



Activated carbon selection

Based on these characteristics, it can be determined which types of molecules are adsorbed by a certain activated carbon. The size of the molecules adsorbed is directly related to the pore size distribution of the activated carbon.

* Dark colors, proteins and foaming agents



Activated carbon characterization

Pore size distribution of a certain activated carbon is responsible for its specific adsorption pattern which is characterized by iodine number, methylene blue adsorption and molasses number.

Applications

Various industries – diverse applications

CARBOFIL™ products can be used as flat sheets in a plate and frame filter such as in the NOVOX® series, or they may be applied as FILTRODISC™ lenticular modules in closed housings such as the DISCSTAR™ series.

	Decolorization	Removal of organic impurities
Biopharmaceutical industry	<ul style="list-style-type: none"> – Albumin – Vitamins – Antibiotics – Vaccines 	<ul style="list-style-type: none"> – Removal of PKA from human plasma fractions – Removal of endotoxins – Removal of organic impurities from contrast liquids
Chemical industry	<ul style="list-style-type: none"> – API – Silicon oils – Solvents – Fine chemicals 	<ul style="list-style-type: none"> – Catalyst recovery – Heavy metal reduction – Removal of organic impurities – Decolorization
Flavors & fragrances industry	<ul style="list-style-type: none"> – Plant / herbal extracts – Fragrances 	<ul style="list-style-type: none"> – Deodorization of ethanol – Removal of pesticides from extracts
Food & beverage industry	<ul style="list-style-type: none"> – Sugar syrup – Spirits – Cider 	<ul style="list-style-type: none"> – Removal of off-tastes from spirits – Removal of bitterness from soups – Decolorization

Convenient media grade selection

CARBOFIL™ products are available with various different grades. To assist in finding the most suitable CARBOFIL™ grade for any application, FILTROX offers the easy-to-use

CARBOFIL™ Test Kit. For further information about the Test Kit contact your local FILTROX representative or our FILTROX experts (applications@filtrox.com).





As a global market leader in depth filtration, FILTROX offers complete solutions for filtration of high value liquids.

We are experts in development, manufacturing and supply of Swiss top quality products for a wide range of applications in pharmaceuticals, biotechnology, chemicals and cosmetics as well as in food and

beverage. Since 1938, we have been developing and manufacturing both filter media as well as filtration equipment in-house. Based on this experience, we can offer our customers a complete range of products.

FILTROX's worldwide distribution network and comprehensive technical support will help you optimize your filtration process.

FILTROX AG

Moosmühlestr. 6
CH-9001 St.Gallen / Switzerland
Phone: +41 071 272 91 11
Fax: +41 071 272 91 00
E-mail: sales@filtrox.ch

FILTROX Southern Europe
Ramón Viñas, 4
08930 Sant Adrià de Besòs / Spain
Phone: +34 934 626 700
Fax: +34 933 810 258
E-mail: filtrox.Espana@filtrox.com

FILTROX UK & Northern Europe
Butts Mill
Barnoldswick
Lancashire
BB18 5HP / United Kingdom
Phone: +44 1282 811000
Fax: +44 1282 811001
E-mail: filtrox.UK@filtrox.com

FILTROX France s.a.r.l.
1 Rue du Claire Matin
F 21200 Beaune / France
Phone: +33 380 222 915
Fax: +33 380 241 856
E-mail: contact@filtroxfrance.com

FILTROX North America
9805 NE 116th Street
PMB A-200
Kirkland WA 98034 / USA
Phone: Toll free 800 473 4526
Phone: +1 425 820 4850
Fax: +1 425 820 2816
E-mail: info@filtroxnorthamerica.com

FILTROX Latinoamerica S.A. de C.V.
Prolongación Recursos Hidráulicos 22, Lote A
La Loma, Tlalnepantla de Baz, CP 54060
Estado de Méxicio, México
Phone: +52 55 2628 1691
E-mail: info@filtrox.com.mx

FILTROX (Shanghai) Filtration System Co., Ltd.
7 # Building no. 1855
TianChen Rd. QingPu
Shanghai 201712 / P.R. China
Phone: +86 021 5922 7510
Fax: +86 021 5922 7511
E-mail: info@filtroxchina.cn

FILTROX Asia-Pacific Pte Ltd
25 International Business Park
#02-14 German Center
Singapore 609916 / Singapore
Phone: +65 93388645
E-mail: sales_apac@filtrox.com